

Solenoid coil VACF-B-C1-1A

Part number: 8030813

FESTO



Data sheet

| Feature | Value |
|----------------------------------|---|
| Type code | VACF |
| Mounting position | Any |
| Duty cycle | 100% |
| Insulation class | H |
| Coil characteristics | 24 V AC: 50/60 Hz, initial power 3.9 VA, holding power 2.6 VA |
| Permissible voltage fluctuations | +/- 10 % |
| Certification | c UL us - Recognized (OL) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Temperature of medium | -20 °C ... 50 °C |
| Degree of protection | IP65 |
| Ambient temperature | -20 °C ... 50 °C |
| Product weight | 54 g |
| Electrical connection | Form C as per EN 175301-803 |
| Type of mounting | With knurled nut |
| Note on materials | RoHS-compliant |
| Housing material | PA Steel |
| Solenoid coil material | Copper Steel Thermoplastic |
| Material of winding | Copper |