

Solenoid coil VACF-A-A1-3W

Part number: 8030828

FESTO



Data sheet

Feature	Value
Type code	VACF
Mounting position	Any
Duty cycle	100%
Insulation class	H
Coil characteristics	230/240 V AC: 50/60 Hz, initial power 3.9 VA, holding power 2.8 VA
Permissible voltage fluctuations	+/- 10 %
Maritime classification	See certificate
CE marking (see declaration of conformity)	As per EU low voltage directive
Certificate issuing authority	DNVGL-TAA000011J
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65
Ambient temperature	-20 °C ... 50 °C
Product weight	79.2 g
Electrical connection	Form A as per EN 175301-803
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplastic
Material of winding	Copper