

Plastic tubing PAN-R-28X2,5-SW

Part number: 8036208

FESTO



Data sheet

Feature	Value
Outside diameter	28 mm
Inside diameter	23 mm
Type code	PAN-R.-SW
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Ambient temperature	-30 °C ... 80 °C
Product weight by length	2.07 kg/m
Pneumatic connection	For plug connection outside diameter 28 mm
Color	Black
Shore hardness	D 62 +/-3
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	TPE-A