



Air preparation combination unit MSB4-1/4:C3:J120-WP

FESTO

Part number: 8042668



Data sheet

| Feature | Value |
|--|--|
| Size | 4 |
| Type code | MSB4 |
| Series | MS |
| Actuator lock | Rotary knob with detent can be closed with accessories |
| Mounting position | Vertical +/- 5° |
| Grade of filtration | 40 µm |
| Condensate drain | Manually rotating |
| Structural design | Shut off valve Filter regulator with pressure gauge |
| Controller function | Outlet pressure constant With primary pressure compensation With secondary exhausting With return flow function |
| Bowl guard | Plastic bowl guard |
| Symbol | 00991755 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 1.5 bar ... 14 bar |
| Pressure regulation range | 0.5 bar ... 7 bar |
| Standard nominal flow rate | 1150 l/min |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Storage temperature | -10 °C ... 60 °C |
| For use in the food industry | See supplementary material information |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 1300 g |
| Type of mounting | With accessories |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | G1/4 |
| Pneumatic connection 3 | G1/4 |
| Housing material | Die-cast aluminum |
| Material of bowl | PC |