

# Sub-base VMPA14-FB-AP-4-1-S1

Part number: 8043929

FESTO



## Data sheet

Feature	Value
Width	65.5 mm
Length	107.3 mm
Width dimension	14.8 mm 14.9 mm
Type code	VPMA14
Max. no. of valve positions	4
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Pilot pressure MPa	0.3 MPa ... 0.8 MPa
Pilot pressure	3 bar ... 8 bar
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	-5 °C ... 50 °C
Product weight	250 g
Pneumatic connection 2	G1/8 M7
Pneumatic connection 4	G1/8 M7
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum