

Fixed flow restrictor VFFG-T-F4-7

Part number: 8047348

FESTO



Data sheet

Feature	Value
Type code	VFFG
Valve function	Flow control function
Type of mounting	Tapped
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Ambient temperature	-5 °C ... 60 °C
Size	For 4 mm diameter
Nominal width	0.7 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Storage temperature	-10 °C ... 60 °C
Product weight	0.4 g
Note on materials	RoHS-compliant