

Common supply manifold OABM-P-G3-15-4

Part number: 8049145

FESTO



Data sheet

Feature	Value
Type code	OABM
Number of device locations	4
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Max. tightening torque	3.3 Nm
Min. tightening torque	0.3 Nm
Product weight	97.1 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/8
Note on materials	RoHS-compliant
Material of sub-base	Wrought aluminum alloy