

Quick coupling plug NPHS-S6-M-G12

Part number: 8059260

FESTO



Data sheet

| Feature | Value |
|---|---|
| Nominal width | 7.85 mm |
| Type code | NPHS |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -10 °C ... 60 °C |
| Nominal tightening torque | 14 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 50 g |
| Pneumatic connection 1 | External thread G1/2 |
| Note on materials | RoHS-compliant |