

# Quick coupling plug NPHS-S6-M-BC9

Part number: 8059265

FESTO



## Data sheet

Feature	Value
Nominal width	7 mm
Type code	NPHS
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	17 g
Pneumatic connection 1	For plug-in sleeve inside diameter 9 mm
Note on materials	RoHS-compliant