

Quick coupling socket NPHS-D6-P-G38

Part number: 8059268

FESTO



Data sheet

Feature	Value
Nominal width	10.2 mm
Type code	NPHS
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Standard nominal flow rate	2033 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	12.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	98 g
Pneumatic connection 1	External thread G3/8
Note on materials	RoHS-compliant