


# Solenoid coil VACF-B-K1-1-10-EX4-M

Part number: 8059806

FESTO



## Data sheet

Feature	Value
Type code	VACF
Mounting position	Any
Switching position indication	no
Min. pick-up time	10 ms
Duty cycle	100%
Coil characteristics	24 V DC: 4.36 W
Permissible voltage fluctuations	+/- 10 %
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX) As per EU RoHS directive
Explosion protection certification outside the EU	EPL Db (BR) EPL Db (CN) EPL Db (IEC-EX) EPL Gb (BR) EPL Gb (CN) EPL Gb (IEC-EX)
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) Zone 1 (BR) Zone 21 (BR) Zone 1 (IEC-EX) Zone 21 (IEC-EX) Zone 1 (CN) Zone 21 (CN)
Certificate issuing authority	DNV17.0013X GYJ17.1077X IBExU 16 ATEX1146X IECEX IBE16.0024X
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex mb IIC T5 Gb
Type of (ignition) protection for dust	Ex mb IIIC T95°C Db
Explosive ambient temperature	-30°C ≤ Ta ≤ +40°C
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65
Ambient temperature	-30 °C ... 40 °C
Product weight	170 g
Electrical connection	3-wire Cable with open end
Cable length	10 m

<b>Feature</b>	<b>Value</b>
Nominal conductor cross section	0.75 mm <sup>2</sup>
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Solenoid coil material	Aluminum Epoxy resin Copper Steel
Material of winding	Copper