

# Plastic tubing PTFEN-5/16-NT-150

Part number: 8063351

FESTO



## Data sheet

Feature	Value
Outside diameter	7.94 mm
Bending radius relevant for flow rate	90 mm
Inside diameter	5.9 mm
Min. bending radius	64 mm
Type code	PTFEN
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight by length	0.049 kg/m
Pneumatic connection	For plug connection outside diameter 5/16"
Color	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS-compliant
Material of pneumatic tubing	PTFE