


# Axial kit EAMM-A-L48-120GA

Part number: 8063490

FESTO



## Data sheet

| Feature                  | Value            |
|--------------------------|------------------|
| Type code                | EAMM-A           |
| Mounting position        | Any              |
| Storage temperature      | -25 °C ... 60 °C |
| Relative air humidity    | 0 - 95 %         |
| Degree of protection     | IP40             |
| Ambient temperature      | -10 °C ... 60 °C |
| Transferable torque      | 17 Nm            |
| Product weight           | 705 g            |
| Interface code, actuator | L48              |
| Interface code, motor in | 120GA            |
| Note on materials        | RoHS-compliant   |