

Axial kit EAMM-A-N38-92RA

Part number: 8063581

FESTO



Data sheet

| Feature | Value |
|--------------------------|------------------|
| Type code | EAMM-A |
| Mounting position | Any |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 60 °C |
| Transferable torque | 12.5 Nm |
| Product weight | 1081 g |
| Interface code, actuator | N38 |
| Interface code, motor in | 92RA |
| Note on materials | RoHS-compliant |