


Axial kit EAMM-A-N80-115GA

Part number: 8063615



Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	60 Nm
Product weight	2212 g
Interface code, actuator	N80
Interface code, motor in	115GA
Note on materials	RoHS-compliant