


Piezo valve VEMP-BS-3-13-D7-F-22T1-P30

Part number: 8064293

FESTO



Data sheet

Feature	Value
Type code	VEMP
Pack size	30
Symbol	00992802
Note on degree of protection	Depending on manifold block
Standard nominal flow rate	19 l/min
Standard nominal flow rate 2-3	20 l/min
Flow direction	Non-reversible
Nominal operating pressure	1 bar
Operating pressure	0 bar ... 1.1 bar
Valve function	3/3, closed, monostable
Nominal width	1.3 mm
Actuation type	Electrical
Pneumatic connection 1	Flange
Pneumatic connection 2	Flange
Pneumatic connection 3	Flange
Medium	Inert gas Air Oxygen (oxygen applications according to IEC 60601-1 only on request) Nitrogen
Special features	Oxygen-compatible as per DIN EN 1797
Operating medium	Compressed air as per ISO 8573-1:2010 [5:3:1]
Information on operating and pilot media	Operation with oil lubrication not possible
Grade of filtration	≤5 μm
Relative air humidity	0 - 70 % Non-condensing
Pressure dew point	≤-20 °C
Max. switching frequency	5 Hz
Temperature of medium	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 70 °C
Storage temperature	-20 °C ... 70 °C
Nominal operating voltage DC	250 V
DC operating voltage range	0 V ... 250 V
Max. current consumption	5 mA
Max. electrical power consumption	0 W
Product weight	8 g
Seals material	EPDM
Housing material	PA-reinforced

Feature	Value
Cover material	PA-reinforced
Note on materials	RoHS-compliant
Width dimension	17.2 mm
Dimensions W x L x H	17.2 mm x 52.1 mm x 7.2 mm
Type of mounting	On terminal strip On sub-base
Mounting position	Any
CE marking (see declaration of conformity)	As per EU low voltage directive