

# Electronics module VMPA14-FB-EMS-D2-8

Part number: 8066766

FESTO



## Data sheet

Feature	Value
Type code	VMPA14
Diagnostics	Condition monitoring Wire break per valve coil Short circuit of pneumatic valves Undervoltage of pneumatic valves
Max. no. of valve positions	4
Max. no. of solenoid coils	8
Intrinsic current consumption at load voltage	3 mA
Intrinsic current consumption at operating voltage	8 mA
Nominal pick-up current per solenoid coil	58 mA to 24 ms
Nominal current with current reduction	9 mA after 24 ms
Corrosion resistance class (CRC)	1 - Low corrosion stress (when installed)
Product weight	30 g
Housing material	POM
Note on materials	RoHS-compliant