

# Reducing sleeve NPFC-R-G14-G18-F

Part number: 8069220

FESTO



## Data sheet

Feature	Value
Type code	NPFC
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar ... 50 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-20 °C ... 150 °C
Product weight	16 g
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/8
Note on materials	RoHS-compliant