


# Pneumatic shock absorber DYSS-G8-2-4-Y1F

Part number: 8073911

FESTO



## Data sheet

Feature	Value
Size	2
Stroke	4 mm
Type code	DYSS-G8
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Symbol	00991495
Max. impact velocity	0.5 m/s
Reset time at room temperature	0.5 s
Reset time at min. ambient temperature	1 s
Mode of operation	Single-acting Pushing
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-10 °C ... 70 °C
Cushioning length	4 mm
Max. stop force	60 N
Max. tightening torque	0.5 Nm
Max. energy absorption per stroke	0.1 J
Max. energy absorption per hour	270 J
Max. residual energy	0.003 J
Resetting force	0.7 N
Product weight	3.9 g
Type of mounting	With threaded sleeve
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel
Piston rod material	High-alloy steel