

Adapter kit DHAA-G-R3-16-B19-16

Part number: 8079175

FESTO



Data sheet

| Feature | Value |
|----------------------------------|----------------------------------|
| Size | 16 |
| Type code | DHAA |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | 0 °C ... 50 °C |
| Product weight | 60 g |
| Type of mounting | With internal thread |
| Adapter plate material | Wrought aluminum alloy, anodized |
| Material of screws | Steel, galvanized |