


Pressure regulator VRPA-LM-N18-T516

Part number: 8086015

FESTO



Data sheet

Feature	Value
Type code	VRPA
Controller function	Outlet pressure constant With secondary exhausting With return flow function
Pneumatic connection 1	1/8 NPT
Pneumatic connection 2	QS-5/16
Type of mounting	Screw-in
Standard nominal flow rate	130 l/min
Ambient temperature	0 °C ... 60 °C
Housing material	PBT
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Mounting position	Any
Actuation type	Manual
Type of seal on screwed trunnion	Coating
Adjusting element	Rotary knob with detent
Symbol	00991558
Rotatability	360 deg/continuous swiveling not permissible
Pressure gauge	with pressure gauge
Pressure regulation range	1 bar ... 7.998 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Product weight	32 g
Material of screwed trunnion	Brass, nickel-plated
Note on materials	RoHS-compliant
Material of threaded seal	PTFE
Static seal material	NBR