

Axial kit EAMM-A-T42-60R

Part number: 8093289

FESTO



Data sheet

Feature	Value
Nominal length	49 mm
Type code	EAMM-A
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	3.2 kgmm ²
Transferable torque	10 Nm
Product weight	349 g
Interface code, actuator	T42
Interface code, motor in	60R
Note on materials	RoHS-compliant