

Axial kit EAMM-A-V25-42AB

Part number: 8094108

FESTO



Data sheet

Feature	Value
Nominal length	36 mm
Type code	EAMM-A
Mounting position	Any
Max. rotational speed	10000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	0.19 kgmm ²
Transferable torque	0.5 Nm
Product weight	75 g
Interface code, actuator	V25
Interface code, motor in	42AB
Note on materials	RoHS-compliant