

Filter flow control CAMF-C6-FD-C6-11A

Part number: 8096867

FESTO



Data sheet

Feature	Value
Short-circuit protection	no
Current rating at 40°C	6 A
Operating voltage range AC	0 V ... 600 V
Nominal inductance	3.7 mH
Nominal inductance tolerance	10 %
Mains frequency	50 Hz ... 60 Hz
Insulation voltage	4000 V
Dimensions W x L x H	60 mm x 80 mm x 116 mm
Certification	ENEC c UL - Recognized (OL)
CE marking (see declaration of conformity)	As per EU RoHS directive
Storage temperature	-10 °C ... 40 °C
Degree of protection	IP00
Ambient temperature	-10 °C ... 40 °C
Product weight	940 g
Type of mounting	Mounting plate, screwed on
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Mounting position	Horizontal
Type code	CAMF
Electrical connection 1, function	Power supply
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, connection technology	Screw terminal
Electrical connection 1, number of pins/wires	6
Electrical connection 1, occupied pins/wires	6
Electrical connection 1, conductor cross section	4 mm ²