

# Parallel kit EAMM-U-87-T46-85AA-114

Part number: 8097655

FESTO



## Data sheet

| Feature                   | Value                  |
|---------------------------|------------------------|
| Size                      | 87                     |
| Center-to-center distance | 114 mm                 |
| Type code                 | EAMM-U                 |
| Mounting position         | Any                    |
| Gear ratio                | 1:1                    |
| Max. rotational speed     | 3000 1/min             |
| Storage temperature       | -20 °C ... 60 °C       |
| Relative air humidity     | 0 - 95 %               |
| Degree of protection      | IP40                   |
| Ambient temperature       | 0 °C ... 50 °C         |
| Mass moment of inertia    | 41.2 kgmm <sup>2</sup> |
| No-load driving torque    | 0.22 Nm                |
| Transferable torque       | 3 Nm                   |
| Product weight            | 986 g                  |
| Interface code, actuator  | T46                    |
| Interface code, motor in  | 85AA                   |
| Note on materials         | RoHS-compliant         |