

Quick coupling EAMC-42-50-12-22-U

Part number: 8099434

FESTO



Data sheet

Feature	Value
Diameter of holder 1	12 mm
Diameter of holder 2	22 mm
Size	42
Nominal length	50 mm
Type code	EAMC
Mounting position	Any
Max. rotational speed	6000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	34.8 kgmm ²
Transferable torque	21 Nm
Product weight	133 g
Note on materials	RoHS-compliant