

Connector plate VABS-B14-T-FN14

Part number: 8099628

FESTO



Data sheet

Feature	Value
Type code	VABS
Mounting position	Any
Structural design	Connection direction upward
Operating pressure	1.5 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 60 °C
Temperature of medium	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
Product weight	192 g
Type of mounting	With through-hole
Pneumatic connection 2	1/4 NPT Flange 1/4 with NAMUR port pattern
Pneumatic connection 4	Flange 1/4 with NAMUR port pattern 1/4 NPT
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Material of sub-base	Wrought aluminum alloy