

# Control plate DADG-FM-F9-VDE2

Part number: 8104802

FESTO



## Data sheet

Feature	Value
Type code	DADG
Based on norm	VDI/VDE 3845 (NAMUR)
Mounting position	Any
Operating pressure	0.2 MPa ... 0.8 MPa
Operating pressure	2 bar ... 8 bar
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Ambient temperature	-20 °C ... 80 °C
Product weight	1340 g
Pneumatic connection	G1/4
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Seals material	EPDM NBR
Threaded pin material	High-alloy stainless steel
Plate material	Wrought aluminum alloy, anodized
Material of screws	High-alloy stainless steel