

# Solenoid coil VACC-S18-120-K4-2U-NM4ME

Part number: 8118178

FESTO



## Data sheet

Feature	Value
Type code	VACC
Actuation type	Electrical
Mounting position	Any
Switching position indication	no
Duty cycle	100%
Insulation class	H
Coil characteristics	110 V AC: 50/60 Hz, power 12.0 VA 110 V DC: 12.0 W
Permissible voltage fluctuations	-15 % / +10 %
Certificate issuing authority	INMETRO DNV 19.0135X
Type of ignition protection for gas	Ex eb mb IIC T4 Gb
Type of (ignition) protection for dust	Ex tb IIIC T120°C Db
Explosive ambient temperature	T4, T120°C: -25°C ≤ Ta ≤ +40°C
Degree of protection	IP66
Product weight	580 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Note on materials	Contains paint-wetting impairment substances RoHS-compliant