

Solenoid coil VACC-S13-18-K4-2U-NM4ME

Part number: 8118325

FESTO



Data sheet

Feature	Value
Type code	VACC
Actuation type	Electrical
Mounting position	Any
Switching position indication	no
Duty cycle	100%
Insulation class	H
Coil characteristics	110 V DC: 1.8 W 110 V AC: 40/65 Hz, power 1.8 VA
Permissible voltage fluctuations	-15 % / +10 %
Certificate issuing authority	INMETRO DNV 17.0042X
Type of ignition protection for gas	Ex eb mb IIC T6, T5, T4 Gb
Type of (ignition) protection for dust	Ex tb IIIC T85°C, T95°C, T130°C Db
Explosive ambient temperature	T4, T130°C: -30°C ≤ Ta ≤ +60°C T5, T95°C: -30°C ≤ Ta ≤ +60°C T6, T85°C: -30°C ≤ Ta ≤ +50°C
Degree of protection	IP65
Product weight	330 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Note on materials	Contains paint-wetting impairment substances RoHS-compliant