

Manifold block-SET VABS-C12-6-S

Part number: 8122790

FESTO



Data sheet

Feature	Value
Width	13 mm
Type code	VABS
Mounting position	Any
Structural design	Connection direction at side
Max. no. of valve positions	Versions according to customer specifications possible
Operating pressure	-0.1 MPa ... 0.7 MPa
Operating pressure	-1 bar ... 7 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:1]
Information on operating and pilot media	Maximum particle size 5 µm
Ambient temperature	5 °C ... 50 °C
Product weight	3 g
Type of mounting	With through-hole
Pneumatic connection 2	For tubing I.D. 4 mm
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Manifold rail material	PBT