

Manifold block VABM-C12-6M-M5-M3-10

Part number: 8122794

FESTO



Data sheet

| Feature | Value |
|--|--|
| Width | 20 mm |
| Type code | VABM |
| Mounting position | Any |
| Structural design | Connection direction downwards |
| Max. no. of valve positions | 10 |
| Operating pressure | -0.1 MPa ... 0.7 MPa |
| Operating pressure | -1 bar ... 7 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [6:4:1] |
| Information on operating and pilot media | Maximum particle size 5 µm |
| Ambient temperature | 5 °C ... 50 °C |
| Product weight | 49.5 g |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | M5 |
| Pneumatic connection 2 | M3 |
| Pneumatic connection 3 | M5 |
| Note on materials | Contains paint-wetting impairment substances RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |