


Hand lever valve H-3-1/4-B

Part number: 8987

FESTO



Data sheet

Feature	Value
Valve function	3/2, bistable
Standard nominal flow rate	600 l/min
Pneumatic working port	G1/4
Operating pressure	-0.95 bar ... 10 bar
Structural design	Plate seat
Nominal width	7 mm
Type code	H
Type of control	Direct
Symbol	00991278
Ambient temperature	-10 °C ... 60 °C
Actuating torque	0.5 Nm
Product weight	320 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Pneumatic connection 3	G1/4
Seals material	NBR
Housing material	Die-cast aluminum