

Bulkhead quick connector SCK-PK-9-KU

Part number: 9390

FESTO



Data sheet

Feature	Value
Nominal width	8 mm
Type code	SCK
Mounting position	Any
Operating pressure for entire temperature range	0 bar ... 10 bar
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection 1	For barbed fitting, inside diameter 9 mm, with union nut
Note on materials	Free of copper and PTFE RoHS-compliant
Housing material	POM