

Adapter AD-G3/8-3/8NPT-I

FESTO

Part number: 9397



Data sheet

Feature	Value
Nominal width	11.5 mm
Type code	AD
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	25 Nm
Max. tightening torque, pneumatic connection 2	22 Nm
Nominal tightening torque	38.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	25.3 g
Pneumatic connection 1	G3/8
Pneumatic connection 2	3/8 NPT
Note on materials	RoHS-compliant