

# Adapter AD-1/4NPT-G1/4-I

Part number: 9625

FESTO



## Data sheet

Feature	Value
Nominal width	7.95 mm
Type code	AD
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	12 Nm
Max. tightening torque, pneumatic connection 2	11 Nm
Product weight	21 g
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	G1/4
Note on materials	RoHS-compliant