

Adapter AD-1/2NPT-G1/2-I

FESTO

Part number: 9627



Data sheet

Feature	Value
Nominal width	14.3 mm
Type code	AD
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	28 Nm
Max. tightening torque, pneumatic connection 2	40 Nm
Product weight	48.48 g
Pneumatic connection 1	1/2 NPT
Pneumatic connection 2	G1/2
Note on materials	RoHS-compliant