

Double nipple E-G1/8-1/8NPT

Part number: 9630

FESTO



Data sheet

Feature	Value
Nominal width	5.95 mm
Type code	E
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	6 Nm
Max. tightening torque, pneumatic connection 2	7 Nm
Nominal tightening torque	10.55 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	9.1 g
Pneumatic connection 1	G1/8
Pneumatic connection 2	1/8 NPT
Note on materials	RoHS-compliant