



Technical Data

Color	Black
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 19.80
Case Weight (lbs)	16.31
Country of Origin	Malaysia
Material	Rubber
Length	14"
Cuff	Straight
Cuff Color	Orange
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

NOVAX®

Class 1 Rubber Insulating Glove with Straight Cuff - 14"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection
- **⚠ WARNING:** Cancer - www.P65Warnings.ca.gov

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Performance Data

Electrical Class	Class 1
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
155-1-14/7	Black	7	616314058738	01616314058645	02616314058644
155-1-14/8	Black	8	616314058745	01616314058638	02616314058637
155-1-14/9	Black	9	616314058752	01616314058683	02616314058682
155-1-14/10	Black	10	616314058769	01616314058690	02616314058699
155-1-14/11	Black	11	616314058776	01616314058591	02616314058590
155-1-14/12	Black	12	616314058783	01616314058584	02616314058583