



## NOVAX®

### Class 0 Rubber Insulating Glove with Straight Cuff - 11"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

## Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

## Technical Data

Color	Yellow
Sizes Available	7-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 12.80
Case Weight (lbs)	10.32
Country of Origin	Malaysia
Material	Rubber
Length	11"
Cuff	Straight
Cuff Color	Yellow
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

## Performance Data

Electrical Class	Class 0
------------------	---------

## Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
170-0-11/7	Yellow	7	616314101465	01616314101464	02616314101463
170-0-11/8	Yellow	8	616314101472	01616314101471	02616314101470
170-0-11/9	Yellow	9	616314101489	01616314101488	02616314101487
170-0-11/9.5	Yellow	9.5	616314154362	01616314154361	02616314154360
170-0-11/10	Yellow	10	616314101434	01616314101433	02616314101432
170-0-11/10.5	Yellow	10.5	616314154355	01616314154354	02616314154353
170-0-11/11	Yellow	11	616314101441	01616314101440	02616314101449
170-0-11/12	Yellow	12	616314101458	01616314101457	02616314101456