



## NOVAX®

### Class 0 Rubber Insulating Glove with Straight Cuff - 11"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meets ANSI/ASTM D120 standard for use around electrical hazards

## Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

## Technical Data

Color	Black
Sizes Available	6-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 12.80
Case Weight (lbs)	10.32
Country of Origin	Malaysia
Material	Rubber
Length	11"
Cuff	Straight
Cuff Color	Black
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

## Performance Data

Electrical Class	Class 0
------------------	---------

## Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
150-0-11/6	Black	6	616314770180	10616314770187	20616314770184
150-0-11/7	Black	7	616314051180	01616314051189	02616314051188
150-0-11/8	Black	8	616314050831	01616314050830	02616314050839
150-0-11/8.5	Black	8.5	616314260537	01616314260536	02616314260535
150-0-11/9	Black	9	616314050848	01616314050847	02616314050846
150-0-11/9.5	Black	9.5	616314260544	01616314260543	02616314260542
150-0-11/10	Black	10	616314050855	01616314050854	02616314050853
150-0-11/10.5	Black	10.5	616314260551	01616314260550	02616314260559
150-0-11/11	Black	11	616314050862	01616314050861	02616314050860
150-0-11/12	Black	12	616314057908	01616314057860	02616314057869