



Cut



Medium Duty

Resilient, cut-resistant polyurethane gloves, with dirt masking for long-lasting wear

- **Heightened durability:** HyFlex® 11-751 PU-coated gloves demonstrate superior durability, with EN level 4 and ANSI level 6 abrasion resistance
- **Advanced protection:** INTERCEPT™ Cut Resistance Technology yarn also grants them EN ISO C/ ANSI 4 cut resistance, making them safer and preventing workplace injuries
- **Considered aesthetics:** HyFlex® 11-751 industrial gloves have been designed with integrated dirt masking, for longer wear
- **Certified performance:** These safety gloves officially comply with Centexbel standards EN 420, for general requirements, and EN 388, for mechanical hazards
- **Guaranteed convenience:** For added practicality, HyFlex® 11-751 industrial working gloves are available in vend pack form, for easy access and re-application

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Automotive Aftermarket

Applications

- General maintenance
- Hardware assembly
- Machining / Stamping / Cutting
- Raw material handling
- Seat and frame build



HyFlex®

ADVANCED MECHANICAL PROTECTION

11-751

INTERCEPT® Cut Resistance Technology in a dirt-masking design

Key Features

- **Durable PU coating:** EN level 4 and ANSI level 6 abrasion resistance
- **INTERCEPT™ Cut Resistance:** EN ISO C/ANSI A4 cut protection
- **Dirt masking:** Stains and marks hidden, ideal for messy applications

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-751	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: HPPE, Fiber glass, Nylon, Spandex Cuff Style: Knitwrist	10	6, 7, 8, 9, 10	224-269mm, 8.81 - 10.59 inches	Black	<ul style="list-style-type: none"> • 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

