



NOVAX®

Class 3 Rubber Insulating Glove with Bell Cuff - 16"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Bell cuff increases comfort on the job
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meets ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Technical Data

Color	Black
Sizes Available	9-11
Packaging	Bagged Each
Packed	6 Pair/Case
Case Dimensions (in)	21.14 x 18.15 x 11.89
Case Weight (lbs)	13.67
Country of Origin	Malaysia
Material	Rubber
Length	16"
Cuff Color	Red
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

Performance Data

Electrical Class	Class 3
------------------	---------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
161-3-16/9	Black	9	616314268489	01616314268488	02616314268487
161-3-16/9.5	Black	9.5	616314268496	01616314268495	02616314268494
161-3-16/10	Black	10	616314268502	01616314268501	02616314268500
161-3-16/10.5	Black	10.5	616314268519	01616314268518	02616314268517
161-3-16/11	Black	11	616314270130	01616314270139	02616314270138