



A CSW Industrials Company

PRODUCT DATA SHEET

COIL-RITE™ Evaporator Coil Cleaner

Description

In just minutes, non-acid COIL-RITE removes grime, oil, grease and dust from air conditioning coils, air handling equipment, as well as electronic and permanent air filters and all mechanical equipment. Powerful surfactant chemicals actually lift grease and dirt off normally inaccessible surfaces. A COIL-RITE cleaning reduces head pressure on over-heated compressors, avoids premature equipment breakdown, increases equipment efficiency and decreases power consumption and costs. It is safe for all metals, including aluminum, when used as directed.

Instructions

Read SDS, all directions, hazard and precautionary statements before using this product.

DIRECTIONS FOR USE:

1. Appropriately dilute with water as needed and detailed below.

For extremely dirty coils & equipment -

1 part COIL-RITE to 4 parts water.

For all types of filters -

1 part COIL-RITE to 5 parts water.

For continuous maintenance -

1 part COIL-RITE to 5-10 parts water.

2. Shut off system. 3. Apply the diluted solution with a trigger sprayer, hand powered tank or high pressure washer. Use a brush to help faster penetration of hard encrusted dirt. 4. Allow 5 to 10 minutes soaking time before rinsing. On an operating evaporator coil, rinsing is not required since the condensate will flush out all the loosened slime and dirt. 5. Rinsing the evaporator coil is not necessary if the unit will be turned on soon after cleaning, but a thorough rinsing with low-pressure water will ensure optimum results.

Applications

Coil-Rite can be safely used on aluminum, copper, stainless steel and painted surfaces. It is formulated to clean metal coils, fiber or metal mesh filters, and other metal surfaces where acids should not be used.



Characteristics | Features

- Cleans grime, oil, grease and dust
- Non-acid, Non- flammable
- Can be used indoors and outdoors
- Will not harm copper or aluminum
- Biodegradable
- Low foam

Packaging

Code	Size	Qty. per Case	Lbs. per Case	Cubic Ft per Case
82612	Gallon (3.8L)	4	36	1.27

Specifications

Wt/Gal @ 77°F	10.0 lbs./gal.
Flash Point SETA CC	None
Color	Green
Shelf Life	2 years



Nonfood Compounds
P1

Suggestions and recommendations covering the use of our products are based on our past experience and laboratory findings. However, as we have no control as to the methods and conditions of application, we only assume responsibility for the uniformity of our products within manufacturing tolerances



WARNING! Causes mild skin and serious eye irritation.

Contains Gylcol Ether 111-76-2 and Surfactant 68412-54-4.

Precautionary Statements PREVENTION: Avoid breathing dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Wash hands thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection. Use only outdoors or in a well-ventilated area.

RESPONSE - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

IF ON SKIN (or hair): Take off all contaminated clothing immediately. Rinse skin with water/shower. Wash all contaminated clothing before reuse.

STORAGE: Store in a well-ventilated place. Keep cool. **DISPOSAL:** Dispose of contents/container to an approved waste disposal plant. **KEEP OUT OF REACH OF CHILDREN.**

FOR CHEMICAL EMERGENCY, SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT,
CALL CHEMTREC - DAY OR NIGHT 1-800-424-9300.

For additional information, refer to Safety Data Sheet, or Call Toll Free
1-800-231-3345

Limited Warranty

RectorSeal, LLC makes the Limited Express Warranty that when the instructions for storage and handling of our products are followed we warrant our products to be free from defects. THIS LIMITED EXPRESS WARRANTY IS EXPRESSLY IN LIEU OF ANY OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, AND OF ANY OTHER OBLIGATION ON THE PART OF RectorSeal, LLC. The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and RectorSeal, LLC shall not be liable for incidental or consequential damages.

Manufactured by

RectorSeal, LLC

2601 Spenwick Drive • Houston, TX 77055, USA • 800-231-3345 • Fax 800-441-0051 • rectorseal.com

A CSW Industrials Company. RectorSeal, the logos and other trademarks are property of RectorSeal, LLC, its affiliates or its licensor's and are protected by copyright, trademark and other intellectual property laws, and may not be used without permission. RectorSeal reserves the right to change specifications without prior notice. ©2020 RectorSeal. All rights reserved. R50128-0720