



AJK 3101

Technical Data

| | |
|----------------------|-----------------------------|
| Color | Green |
| Sizes Available | S-2XL |
| Packaging | Bulk Pack |
| Packed | 12 Dozen/Case |
| Case Dimensions (in) | 14.17 x 11.42 x 11.42 |
| Case Weight (lbs) | 22.71 |
| Country of Origin | Sri Lanka |
| Polymer | Nitrile |
| Thickness | 15 Mil |
| Lining | Unlined |
| Length | 13" |
| Cuff | Straight |
| Grip | Raised Diamond |
| Dip | -- |
| Construction | Unsupported |
| Certifications | 21 CFR, CFIA, Silicone Free |
| Product Circularity | -- |

Assurance®

Unsupported Nitrile, Unlined with Raised Diamond Grip - 15 Mil

- Medium weight construction and hand specific design provide real comfort with protection
- Provides flexibility, tactile sensitivity and dexterity sometimes lacking in heavier gauge unsupported nitriles
- Provides the protection from chemical and physical hazards not always found in thinner gauge nitrile disposables
- Unlined to reduce potential of product contamination
- Straight cuff adds additional length to protect the forearm from liquid run-off
- Raised Diamond pattern for an enhanced grip

Applications

- Cleaning
- Laboratory Analysis
- Printing Industries
- Agrochemicals
- Assembly

Performance Data

| | |
|-----------------------|-------|
| ANSI Cut Level (2016) | -- |
| EN 388 | 3101X |
| EN 374-5 | -- |

Care Instructions



Do Not Wash



SKU Information

| SKU | COLOR | SIZE | UPC | UPC (INNER) | UPC (CASE) |
|--------------|-------|------|--------------|----------------|----------------|
| 50-N140G/S | Green | S | 616314035890 | 01616314035890 | 02616314035890 |
| 50-N140G/M | Green | M | 616314035883 | 01616314035883 | 02616314035883 |
| 50-N140G/L | Green | L | 616314035876 | 01616314035876 | 02616314035876 |
| 50-N140G/XL | Green | XL | 616314035906 | 01616314035906 | 02616314035906 |
| 50-N140G/XXL | Green | 2XL | 616314035913 | 01616314035913 | 02616314035913 |