



Technical Data

| | |
|----------------------|-----------------------|
| Color | Brown |
| Sizes Available | S-XL |
| Packaging | Bulk Pack |
| Packed | 10 Dozen/Case |
| Case Dimensions (in) | 26.38 x 11.02 x 12.99 |
| Case Weight (lbs) | 44.09 |
| Country of Origin | India |
| Hide | Split Cowhide |
| Grade | Regular |
| Cuff | Slip-on |
| Stitching | Nylon |
| Thumb | Straight |
| Construction | Cut-and-Sewn |
| Certifications | -- |
| Product Circularity | -- |

PIP®

Regular Grade Split Cowhide Leather Drivers Glove - Straight Thumb

- Split Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Split leather is economical and has a visible texture
- Drivers gloves feature slip-on styling to provide good fit and comfort
- Straight thumb increases comfort in closed-fisted work
- Elastic closure sewn inside glove for safety and comfort
- Color coded hems for easy size identification
- **⚠️ WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Performance Data

| | |
|---------------------|----|
| ANSI Cut Level | -- |
| ANSI Puncture Level | -- |
| EN 388 | -- |

Care Instructions



Do Not Wash

Applications

- General Applications
- Construction Applications
- Roofing
- Farming
- Utility Work
- Roping



SKU Information

| SKU | COLOR | SIZE | UPC | UPC (INNER) | UPC (CASE) |
|-----------|-------|------|--------------|----------------|----------------|
| 69-138/S | Brown | S | 616314008634 | 01616314008634 | 02616314008634 |
| 69-138/M | Brown | M | 616314008641 | 01616314008641 | 02616314008641 |
| 69-138/L | Brown | L | 616314008658 | 01616314008658 | 02616314008658 |
| 69-138/XL | Brown | XL | 616314008665 | 01616314008665 | 02616314008665 |