



Evolution® Deluxe 6161

Vented, Full Brim Hard Hat with HDPE Shell, 6-Point Polyester Suspension and Wheel Ratchet Adjustment

- High-Density Polyethylene (HDPE) shell with a full brim providing additional protection against sun, glare, rain and falling debris
- Extended back brim helps protect neck and ears from the sun's UV rays, as well as a run-off for rain and snow...short front brim shades the face while allowing excellent visibility
- Brim includes finger grips on front and rear, as well as a textured underside to reduce reflection/glare
- 6-Point suspension system with polyester textile straps offers unrivaled comfort without compromising performance
- Unique "3D Adjustment" provides a precise fit using harness depth settings...unlike any other hard hat on the US market today
- Revolution™ Wheel Ratchet is easy to use and creates a firm comfortable fit
- **⚠️ WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



Technical Data

Color	Blue, Gray, Green, Red, White, Yellow, Neon Orange, Neon Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	22.05 x 12.60 x 18.90
Case Weight (lbs)	11.07
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Vented
Brim Style	Full
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Chin Strap	--
Sweatband	Chamlon
Construction	--
Certifications	ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
CSA Type	--
Electrical Class	Class C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-23



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6161V-50	Blue	OS	5038428011228	5038428812726	5038428812726
280-EV6161V-40	Gray	OS	5038428163361	5038428813556	5038428813556
280-EV6161V-30	Green	OS	5038428011211	5038428812719	5038428812719
280-EV6161V-OR	Neon Orange	OS	5038428011259	5038428812757	5038428812757
280-EV6161V-LY	Neon Yellow	OS	5038428011266	5038428812764	5038428812764
280-EV6161V-60	Red	OS	5038428011235	5038428812733	5038428812733
280-EV6161V-10	White	OS	5038428011198	5038428812696	5038428812696
280-EV6161V-20	Yellow	OS	5038428011204	5038428812702	5038428812702