



Technical Data

Color	Orange
Sizes Available	6-12
Packaging	Boxed
Packed	12 Pair/Case
Case Dimensions (in)	16.93 x 16.93 x 12.80
Case Weight (lbs)	9.72
Country of Origin	Malaysia
Material	Rubber
Length	11"
Cuff	Straight
Cuff Color	Orange
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

NOVAX®

Class 00 Rubber Insulating Glove with Straight Cuff - 11"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection
- **⚠️ WARNING:** Cancer - www.P65Warnings.ca.gov

Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

Performance Data

Electrical Class	Class 00
------------------	----------

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
147-00-11/6	Orange	6	616314770142	10616314770149	20616314770146
147-00-11/7	Orange	7	616314050749	01616314050748	02616314050747
147-00-11/8	Orange	8	616314038020	01616314038020	02616314038020
147-00-11/9	Orange	9	616314038037	01616314038037	02616314038037
147-00-11/10	Orange	10	616314038044	01616314038044	02616314038044
147-00-11/11	Orange	11	616314038051	01616314038051	02616314038051
147-00-11/12	Orange	12	616314057830	01616314058621	02616314058620