



## Technical Data

Color	Salt & Pepper
Sizes Available	XS-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	11.81 x 12.60 x 14.17
Case Weight (lbs)	11.02
Country of Origin	China
Liner Material	Dyneema Diamond Technology
Coating	Polyurethane
Coating Color	Gray
Coating Coverage	Palm & Fingers
Grip	Flat
Gauge	13
Cuff	Knit Wrist
Impact Protection	--
Construction	Coated Seamless Knit
Certifications	--
Product Circularity	Reusable / Launderable Recycled via Terracycle

## G-Tek® 3GX®

Seamless Knit Dyneema® Diamond Blended Glove with Polyurethane Coated Flat Grip on Palm & Fingers

- Seamless construction offers increased comfort and breathability
- Dyneema®, Polyester & Spandex shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Polyurethane coatings take on the surface properties of the glove liner providing a tactile grip in dry and slightly oily conditions, ideal for applications that require dexterity for precise handling
- Knit Wrist helps prevent dirt and debris from entering the glove
- Color coded hems for easy size identification
- Washable, resistant to chemicals, water, and ultraviolet light
- **⚠️ WARNING:** Cancer - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

## Applications

- Thin Coating, Good Grip for High Dexterity Handling
- Maintenance and Repair Operations
- Handling, Assembly and Sorting of Small to Medium Parts and Materials
- Shipping, Receiving and Packaging

## Performance Data

ANSI Cut Level (2016)	A3
ANSI Abrasion Level	4
ANSI Puncture Level	--
ANSI Impact Level	--
ANSI Contact Heat Level	--
EN 388	4442CX
EN Abrasion Level	4
EN Cut Level	4
EN Tear Level	4
EN Puncture Level	2
ASTM F1358 Vertical Flame Level	--

## Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

**PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®**

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobalsafety.com](http://www.pipglobalsafety.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-04



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
19-D320/XS	Salt & Pepper	XS	616314095894	01616314095893	02616314095892
19-D320/S	Salt & Pepper	S	616314095870	01616314095879	02616314095878
19-D320/M	Salt & Pepper	M	616314095863	01616314095862	02616314095861
19-D320/L	Salt & Pepper	L	616314095856	01616314095855	02616314095854
19-D320/XL	Salt & Pepper	XL	616314095887	01616314095886	02616314095885
19-D320/XXL	Salt & Pepper	2XL	616314095900	01616314095909	02616314095908