



Zenon Z14SN™

Rimless Safety Glasses with Black Temple, Silver Mirror Lens and Anti-Scratch Coating

- Lightweight, rimless design provides all day user comfort
- Flexible, rubber tip temples provide a secure fit without uncomfortable pressure points
- Soft rubber bridge design with a ribbed nosepiece for comfort
- 10 Base curve lens
- Meets ANSI Z87.1+
- **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Outdoor Work
- Drivers
- Marine
- Drilling Rig



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	25.59 x 10.63 x 12.60
Case Weight (lbs)	15.43
Country of Origin	Malaysia
Lens	Mirror
Frame Style	Rimless
Lens Color	Silver
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Rubber
Temple	Rubber Tips
Diopter	--
Base Curve	10
Construction	--
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

Care Instructions

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2023-05-19



SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS COATING	UPC	UPC (INNER)	UPC (CASE)
250-08-5509	Amber	Tinted	Amber	AS/AF	616314161971	01616314161970	02616314161979
250-08-0001	Black	Tinted	Gray	AS	616314077807	01616314077806	02616314077805
250-08-0005	Black	Mirror	Silver	AS	616314077845	01616314077844	02616314077843
250-08-0021	Black	Tinted	Gray	AS/AF	616314077814	01616314077813	02616314077812
250-08-0000	Clear	Clear	Clear	AS	616314077791	01616314077790	02616314077799
250-08-0002	Clear	I/O	Clear	AS	616314077838	01616314077837	02616314077836
250-08-0020	Clear	Clear	Clear	AS/AF	616314077821	01616314077820	02616314077829
250-08-5503	Light Blue	Tinted	Light Blue	AS	616314186554	01616314186553	02616314186552

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated